

TOPDENT SPEZIALFRÄSER FÜR PEEK, PMMA & NYLON

NEU




Die spezielle Verzahnung erlaubt einen schnellen Materialabtrag mit scharfem Schnitt ohne Materialerhitzung. Es entsteht eine glatte Materialoberfläche, sodass diese anschließend leicht poliert werden kann.

Geeignet zur schonenden Bearbeitung von PEEK, PMMA und Nylon etc., sowie aller thermoplastischen und weichbleibenden Kunststoffen. Die Fräser eignen sich zum Trennen der Haltestege, Verschleifen der Ansatzstellen der Haltestege, zur Korrektur von Unebenheiten in der Formgebung, als auch zur Ausarbeitung von Zahnfleischmasken.


Wichtig: Nur mit leichtem Anpressdruck arbeiten!

- 1) max. 12.000 min⁻¹
- 2) max. 18.000 min⁻¹
- 3) max. 20.000 min⁻¹



**Kreuzverzahnung
mit Querhieb**

1 Stück



Set: alle 8 Fräser auf SteWaFix-
Instrumentenständer

REF 20560S



TOPDENT SPECIAL CUTTERS

FOR PEEK, PMMA & NYLON


NEW



The special cut enables a fast material removal with sharp cut without heating the material. The result is a smooth surface on the material, which can then be easily polished.

Suited for working on PEEK, PMMA and nylon etc., as well as for all thermoplastic and soft acrylics. Cutters are suited for separating retention bars, reducing their stubs, for adjusting uneven areas in the shape and also for gingival masks.


Important: only apply light pressure during trimming.



Cross cut,
transverse

- ¹⁾ max. 12'000 rpm⁻¹
- ²⁾ max. 18'000 rpm⁻¹
- ³⁾ max. 20'000 rpm⁻¹

1 pc.



Set of all 8 cutters on a SteWaFix bur rack

REF 20560S



M070925 12.02.2020